



Wattstopper
Wattstopper PLUS Ceiling Mount Wireless Sensor/Photocell, 1500 square feet
Part No. BCS_WA_EN-SCPPH-1500-ZB

The EN-SCPPH-1500-ZB is a ceiling/surface mount sensor that combines both Passive Infrared (PIR) and Photocell sensing into a single device. With a range of 1500 sq. ft., the Wireless Sensor connects to the Wattstopper PLUS system via Zigbee



Features & Benefits

Occupancy Sensor & Photocell built into one device	Simple Installation, using magnetic mounting and 360 degree directional flexibility
Reposition sensor with no noticeable substrate marks	Wireless sensor offers 10-year battery life
Customize time-out settings and monitor battery life using the Wattstopper PLUS Software	

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	840356700144	Country Of Origin	Canada
Features	Flame Retardant	Installation Location	Ceiling
Included	Battery, Decorator Strap, Mounting Screws, Sensor Mask	Application Sector	Commercial, Industrial
Warranty Type	5-Year	Type	Sensor

Dimensions

Product Width US	6.37 in	Product Weight US	0.5 lb
Product Height US	1.13 in	Product Length US	3.37 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

cUL Listed	Yes		
------------	-----	--	--

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Antenna Gain	1.1 dBi	Has Battery	Yes
--------------	---------	-------------	-----

Sensor Coverage Pattern	360 deg	Battery Capacity	2200 mAh
-------------------------	---------	------------------	----------

Sensor Type	Daylight, Occupancy	Sensor Mounting Height	8-10 ft
-------------	---------------------	------------------------	---------

Wireless Range	Zigbee, up to 100 ft	Sensor Technology	Passive Infrared (PIR)
----------------	----------------------	-------------------	------------------------

Topology	Wireless Mesh	Indoor/Outdoor	Indoor
----------	---------------	----------------	--------

Sensor Coverage	1500 sq ft	Battery Life	Up to 10 Years
-----------------	------------	--------------	----------------

Mounting Type	Magnetic, Surface Mount	On Function	Selectable Auto/Manual
---------------	-------------------------	-------------	------------------------

Current Draw	3 mA	Battery	2 AA
--------------	------	---------	------

Operating Temperature	32°-104°F	Operating Humidity	0-90% RH (Non-Condensing)
-----------------------	-----------	--------------------	---------------------------

Sensing Range	40 ft	Antenna Pattern	Omni-directional
---------------	-------	-----------------	------------------
