



Wattstopper
Wattstopper PLUS Wireless Wallstation, 2 Button, Ivory
Part No. BCS_WA_EN-WS-2B-ZB-IV



The WS Standard Wallstation Series consists of a two-button and a four-button wallstation that enable essential lighting control. The 2-button wallstation is a single zone manual controller ideal for conference rooms, private offices, classrooms, and other similar spaces. A short press of the upper/ lower buttons turns lighting ON/OFF, while a "press and hold" dim lighting up or down. The 4-button wallstation is a single zone manual controller ideal for conference rooms, libraries, and other similar spaces. It has a dedicated button for ON, OFF, and for raise/lower functionality with intuitive button engraving. The WS Standard Series Wallstations are available in wired and wireless options.

Features & Benefits

The sleek, aesthetic designs are suitable for all interior locations

Setup and monitoring via Polaris software with easy mapping/re-mapping

10-year battery life for wireless version with automatic battery monitoring via Polaris software

Specifications

General Info

Product Line	Wattstopper	Color	Ivory
Finish	Plastic	UPC Number	840356701875
Country Of Origin	Canada	Switch Type	Push
Application Sector	Commercial	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	2.76 in	Product Weight US	0.35 lb
Product Depth US	0.94 in	Product Height US	4.5 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

cUL Listed	Yes
------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---------------------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Has Battery	Yes
---------------------------	--------	-------------	-----

Battery Capacity	3 V	Frequency Band	2.4 GHz
------------------	-----	----------------	---------

Operating Temperature Max	40 °C	Number of Buttons	2
---------------------------	-------	-------------------	---

Number of Rockers	0	Wireless Range	Zigbee, up to 100 ft
-------------------	---	----------------	----------------------

Input Voltage	3 VDC	Indoor/Outdoor	Indoor
---------------	-------	----------------	--------

Battery Life	Up to 10 Years	Mounting Type	Surface
--------------	----------------	---------------	---------

Battery	2 AA	Operating Temperature	-10°-40°C
---------	------	-----------------------	-----------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Wireless
--------------------	---------------------------	----------------------	----------

Antenna Pattern	Omni-directional	Engraving Type	Icon
-----------------	------------------	----------------	------
