



**Wattstopper**  
**Wattstopper PLUS Wireless Scene Dimming Wallstation, 5 Button, Ivory**  
Part No. BCS\_WA\_EN-WS-SC5-ZB-IV



The SC Scene Dimming Wallstation series is a multi-scene, single-zone dimming Wallstation that provides customized light level control in areas such as boardrooms, conference rooms, private offices, and other areas requiring architectural dimming. The SC Series allows the user to select pre-programmed light levels or "scenes" with the push of a button. Scene configuration can be changed via Software.

## Features & Benefits

The sleek, aesthetic designs are suitable for all interior locations

Setup and monitoring via Polaris software with easy mapping/re-mapping

10-year battery life for wireless version with automatic battery monitoring via Polaris software

## Specifications

### General Info

Product Line	Wattstopper	Color	Ivory
Finish	Plastic	UPC Number	840356702131
Country Of Origin	Canada	Switch Type	Push, Rocker
Number of Switches	6	Application Sector	Commercial
Warranty Type	5-Year	Type	Switch

### Dimensions

Product Width US	2.76 in	Product Weight US	0.35 lb
Product Depth US	0.94 in	Product Height US	4.5 in

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

---

cUL Listed	Yes
------------	-----

---

### Additional Information

---

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

---

### Technical Information

---

Operating Temperature Min	-10 °C	Compatibility	Wattstopper PLUS Wireless, Zigbee
---------------------------	--------	---------------	-----------------------------------

---

Has Battery	Yes	Number of Connections	0
-------------	-----	-----------------------	---

---

Battery Capacity	3 V	Frequency Band	2.4 GHz
------------------	-----	----------------	---------

---

Operating Temperature Max	40 °C	Number of Buttons	5
---------------------------	-------	-------------------	---

---

Number of Rockers	1	Wireless Range	Zigbee, up to 100 ft
-------------------	---	----------------	----------------------

---

Antenna	Integrated, Internal	Input Voltage	3 VDC
---------	----------------------	---------------	-------

---

Indoor/Outdoor	Indoor	Battery Life	Up to 10 Years
----------------	--------	--------------	----------------

---

Mounting Type	J-Box, Surface	Battery	2 AA
---------------	----------------	---------	------

---

Operating Temperature	-10°-40°C, 14°-104°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	----------------------	--------------------	---------------------------

---

Wire Connection Type	Wireless	Antenna Pattern	Omni-directional
----------------------	----------	-----------------	------------------

---

Engraving Type	Icon with Text
----------------	----------------

---