




Wattstopper
Wattstopper PLUS Wireless Zone Control Wallstation, 6 Button, Gray
Part No. BCS_WA_EN-WS-ZC6-ZB-GR



The ZC Zone Controller Wallstation series is a multi-zone Wallstation that offers software configurable lighting control that provides ON/OFF switching for multiple lighting zones. It is generally located at entry points to a floor or department and is used to activate or deactivate a lighting zone. The zone status is indicated by an LED display with white indicating ON and blue indicating OFF.

Features & Benefits

The sleek, aesthetic designs are suitable for all interior locations

Setup and monitoring via Polaris software with easy mapping/re-mapping

10-year battery life for wireless version with automatic battery monitoring via Polaris software

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Plastic	UPC Number	840356702322
Country Of Origin	Canada	Switch Type	Push
Number of Switches	6	Application Sector	Commercial
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	2.76 in	Product Weight US	0.35 lb
Product Depth US	0.94 in	Product Height US	4.5 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

cUL Listed	Yes
------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Operating Temperature Min	-10 °C	Compatibility	Wattstopper PLUS Wireless, Zigbee
---------------------------	--------	---------------	-----------------------------------

Has Battery	Yes	Number of Connections	0
-------------	-----	-----------------------	---

Battery Capacity	3 V	Frequency Band	2.4 GHz
------------------	-----	----------------	---------

Operating Temperature Max	40 °C	Number of Buttons	6
---------------------------	-------	-------------------	---

Number of Rockers	0	Wireless Range	Zigbee, up to 100 ft
-------------------	---	----------------	----------------------

Antenna	Integrated, Internal	Input Voltage	3 VDC
---------	----------------------	---------------	-------

Indoor/Outdoor	Indoor	Battery Life	Up to 10 Years
----------------	--------	--------------	----------------

Mounting Type	Surface	Battery	2 AA
---------------	---------	---------	------

Operating Temperature	-10°-40°C, 14°-104°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	----------------------	--------------------	---------------------------

Wire Connection Type	Wireless	Antenna Pattern	Omni-directional
----------------------	----------	-----------------	------------------

Engraving Type	Icon
----------------	------
