



Pass and Seymour  
Wide Slide Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer, Non-Preset, White  
Part No. WSCL450W



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

Convenient Operation - Combines ON/OFF Decorator-style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products

Higher ratings

Single-pole operation

Screw-pressure-plate back wire terminals save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Switch Type	Slider
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

### Technical Information

---

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Bulb Compatibility	CFL, Incandescent, LED	Number of Poles	3-Way, Single Pole
Wattage	450 W	Voltage	120 V
Load	CFL, LED	Environmental Conditions	Humidity: Less than 95% non condensing

---