
Ortronics

Infinium Quantum M4 Splice Cassette, 12F, LC Duplex, OM4, Ribbon

Part No. M4LCD12-50ER4A1



Infinium Quantum Splice Cassettes are available in the Infinium M4 footprint, enabling industry leading performance, fast field termination, and providing cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations.

Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel

Clear Top: Enables fast and easy fault identification

Front or Rear Mounting: Simplify installation by mounting from the front or rear of the? enclosure panel

Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager

Installation Convenience: Do all splicing and managing work outside the enclosure

Compact: These Splice cassettes provide a very compact splicing solution

Flexible Install: Mount from the front or rear of an enclosure or panel

Specifications

General Info

Product Line	TBD	Color	Black
Hazardous Materials	No	Included	(12 or 24) Fiber Pigtails, Splice Protection Sleeves, Splice Management Tray, Adapter Panel, Protective Dust Caps
Application Sector	Commercial	Standard	TIA-568-C.3
Type	Cassette		

Dimensions

Product Width US	4.19 in	Product Weight US	1.0 lb
Product Depth US	6.18 in	Product Height US	1.24 in

Technical Information

Compatibility	Infinium HD-E / Infinium Panel	Number of Ports	12
Connector Type	LC Duplex	Performance Level/Tier	Infinium Quantum