On-Q
2-Way Digital Cable Splitter with Coax Network Support
Part No. VM2202V1



This professional-grade digital cable splitter distributes HDTV Antenna/Digital Cable and coax data network signals to two devices. Ideal for MoCA-capable networks.

Features & Benefits

Exceeds the performance standards set by major cable providers

6kV Surge Protection on all ports

Insertion Loss: 201 - 3.6 dB, 41 - 5 dB, 551 - 751 dB, 1125 - 1326 dB

Compatible with existing and future networks such as MoCA, VoIP, and DOCSIS 3.0

Coax networking adapters and splitters are not compatible with satellite television systems

Specifications

General Info

Product Line	On-Q	UPC Number	804428066231
Country Of Origin	China	Application Sector	Residential

Technical Information

Connector	ANSI/SCTE 01 Compliant ECT F-port	Temperature Rating	-40° - 60° C
Return Loss	INPUT, 5-14MHz: 25dB, 15-200MHz: 30dB, 201-550MHz: 22dB, 551-1002MHz: 20dB. OUTPUT, 5-14MHz: 28dB, 15-40MHz: 35dB, 41-200MHz: 30dB, 201-550MHz: 25dB, 551-1002MHz: 20dB	Impedance	75 ohms