Pass and Seymour

Discontinued - Specification Grade Decorator Switch, Ivory

Part No. 2601347I



Single Pole, Back and Side Wire, Canadian Decorator Switch, 15 amps, 347 volts, Ivory.

Features & Benefits

Impact-resistant polycarb back body and frame.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Integral auto-ground clip for positive ground to metal boxes.

Tri-drive ground, terminal, and mounting screws.

All terminal screws backed out, ready-to-install.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007260014
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Industrial
Standard	UL 20	Type	Switch

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

Technical Information

Operating Temperature Min	-4 °F	Contact Rating	15amp, 347vac
Operating Temperature Max	140 °F	Amperage	15 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Operating Temperature	-4°-140°F (-20°-60°C)	Voltage	347.0 V