# 

radiant Collection radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Brown Part No. 1597TR



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Conducts an industry-leading automatic self-test every 3 Unlike breaker alternatives, GFCI receptacles make it easier to fix seconds. If the device ever fails, the indicator light flashes to trips with a reset button right on the device. signal it should be replaced. Equipped with proven SafeLock protection feature: if critical Extends GFCI protection to "downstream" outlets when used components are damaged and protection is lost, power to the with feed-thru wiring configuration. Note: Will cut power to face outlet is disconnected. and downstream outlets if wired incorrectly. Protects children with a patented tamper-resistant shutter Replaces any standard receptacle with ease, in as little as 10 system that prevents improper insertion of foreign objects, minutes. complete with "invisi-shutters" for an invisible effect. Features durable, high-impact resistant thermoplastic More color options available to fit any style, including finishes to construction. match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available

## Specifications

from the radiant® Collection.

#### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Brown	Finish	Matte
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Туре	Outlet		

#### Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party	Agencies		
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2