




radiant Collection  
radiant® 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, White  
Part No. 2097W



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device	Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced
Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected	Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly
Replaces any standard receptacle with ease, in as little as 10 minutes	Features durable, high-impact resistant thermoplastic construction
More color options available to fit any style, including finishes to match current hardware and lighting trends	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Indoor, Residential, Self-Test
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

---

Product Width US	1.73 in	Product Depth US	1.03 in
------------------	---------	------------------	---------

---

Product Height US	4.2 in
-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Number of Gangs	1	Amperage	20 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

NEMA Configuration Code	5-20R	Mounting Type	Box
-------------------------	-------	---------------	-----

---

Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2
---------	---------	--------------------------	------------------------

---