adorne Collection

adorne® 15A Tamper-Resistant Dual-Controlled Outlet, Graphite

Part No. ARCD152G10

A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Independently cut power to either plug when not in use to conserve energy.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
UPC Number	785007234558	Country Of Origin	China
Number of Receptacles	2	Device Front Face Size	Full-Size
Device Backbody Size	Full-Size	Outlet Type	Tamper-Resistant
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	1.77 in	Product Depth US	1.73 in

Product Height US	2.12 in

Technical Information

Is Tamper-Resistant	Yes	Connection	Side and Back Wire
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Mounting Type	Box	Connection Type	Internal Pressure Plates
Environmental Conditions	95% (relative humidity, non-condensing)		