Pass and Seymour

Heavy Duty, Short Length, Rotating Eye, K-Type

Part No. PS0502

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 0.500-0610-inch, Mesh Length - 16-inch, Eye Diameter - 7/8-inch, Break Strength - 5,600 lbs.

Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 16: Eye Diameter: 7/8

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994070
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	0.5 in	Minimum Cable Range	0.61 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations