Pass and Seymour

PlugTail® Hospital-Grade 15A USB Charging Receptacles, Red

Part No. PTTR15HACUSBRED

PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of todays mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides Ale power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

- AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects
- Triple-wipe, brass line contacts for 15A commercial applications
- Zinc-plated steel for corrosion resistance
- PlugTail termination allows for more productive, finger-safe installation and added future flexibility
- Available in 15 & 20A, Specification Grade and Hospital Grade configurations
- Efficient, 15.5W power supply for fast charging of mobile phones and tablets
- Multiple color options available
- 5Vdc Type-C USB port to charge USB Type-C compatible mobile devices
- Stainless steel auto-ground clips assure positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007113372	Country Of Origin	China

Dimensions

Product Width US	1.693 in	Product Depth US	1.45 in
Product Height US	2.677 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Amperage	15 A