




Wiremold
880CS2-NA - Omnibox Series Cast-Iron Floor Box
 Part No. 880CS2-NA



The 880CS2 Omnibox Floor Box Series provides an excellent activation solution for applications where single service is required in open space areas. The 880CS2 floor box is offered in a durable cast iron construction, designed to be installed in above grade concrete floor applications and to meet a wide range of market requirements.

This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

Country of Origin: USA.

Features & Benefits

TopGuard protection. All cover assemblies for the Omnibox Floor Box Series have TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments.

Fully adjustable box. Before and after concrete pour adjustability. Lower installed cost.

Watertight cast-iron construction. Meets requirements for on grade or below grade application.

Two-gang configurations, maximum flexibility. Can remove divider for greater capacity. Supports multiservice applications.

Boxes and covers have been listed by Underwriters Laboratories Inc. to their standard UL514A, 514C, 514D, and Canadian standard C22.2

Flush activation assemblies for carpet and tile. Aesthetically pleasing assemblies are interchangeable for both cast-iron and stamped steel.

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use. A wide selection of data and bezel options available for use with Ortronics TracJack and Series II devices.

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564080428
Country Of Origin	United States	Construction	Assembled
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.

Type	Floor Box
------	-----------

Dimensions

Product Width US	5.38 in	Product Weight US	9.66 lb
------------------	---------	-------------------	---------

Product Volume US	174.6 cu in	Product Depth US	9.63 in
-------------------	-------------	------------------	---------

Product Height US	3.38 in	Cubic Capacity	117 cu in
-------------------	---------	----------------	-----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Cable Entry	Knockouts	Number of Outlets	4
-------------	-----------	-------------------	---
