



Wiremold  
Evolution™ Series 4-Gang Hinged Wall Box  
Part No. EHWB4-WH



Designed to fit into the 16" on center (406mm) opening between studs in a standard 2"x 4" (51mm x 102mm) wall. For both new work and old work applications. The box has 4-gang standard NEMA size openings and is designed to accommodate power, communications, and A/V devices. The box has been designed with a cable pass-through capability, allowing multiple service access points to be daisy chained together, eliminating the need for multiple conduit runs. Box includes temporary cover. Finished cover assembly (EHWB4C) sold separately.

## Features & Benefits

Available in both 4- and 8-gang versions to provide maximum flexibility.

Cover opens a full 180° and can be painted to blend with room decor. Includes integrated handle, lock and key set for security, and flush egress door for cabling.

Accepts Legrand AVIP devices, plus A/V devices from leading manufacturers.

Accepts trade size service feeds from 3/4" up to 2". Knockout plates are removable and interchangeable, providing multiple options.

Both boxes (4- and 8-gang) fit are designed to fit in 16" opening between studs in standard 2" x 4" [51mm x 102mm] wall.

Finished interior eliminates industrial look for upscale installations, while increasing visibility, making it easier to locate.

Built-in tunnel & feed through capability allows service feeds to be fed through the box, reducing the number of feeds required to reduce installation time.

Designed to accept standard 1- to 4-gang device plates. No proprietary plates simplifies ordering and installation.

3 5/8" [92mm] of space behind device plates provides the extra depth needed for wiring larger A/V devices.

Can be installed in new work and old work installations. New hardware not necessary.

UL Listed to U.S. and Canadian safety standards.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564085577
Country Of Origin	United States	Construction	Assembled
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.

---

Type	Floor Box
------	-----------

---

### Dimensions

---

Product Width US	7.98 in	Product Depth US	3.98 in
------------------	---------	------------------	---------

---

Product Length US	10.98 in	Cubic Capacity	56.9 cu in
-------------------	----------	----------------	------------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Cable Entry	Knockouts	Number of Outlets	4
-------------	-----------	-------------------	---

---