




radiant Collection
radiant® Smart Switch with Zigbee 3.0, White
Part No. WZ3RL10WH



Elevate every experience with Smart Hospitality Solutions by Legrand. Usable on its own or combined with Legrand's complete Smart Hospitality offering, this Smart Switch lets you select custom settings behind-the-scenes to automate and adjust a room's lighting, enhancing the guest experience while also helping you manage energy and cost. As part of Legrand's collections of designer switches and outlets, the Smart Switch with Zigbee 3.0 pairs its advanced functionality with exceptional style, to further set your brand apart. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Automatically turn lights on or off, perfect for enhancing guest comfort and managing energy usage.

Pair with Smart Motion or Door Sensors with Zigbee 3.0 to create scenes based on occupancy levels.

Integrate with the Smart Thermostat with Zigbee 3.0 Hub and other devices for a complete Smart Hospitality Solution.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Supports multiple load types such as LED, incandescent, electronic, inductive and 1/2 HP motors

Compatible with Zigbee 3.0, and the older Zigbee 1.2HA standard. Also IEEE 802.15.4 compliant.

Replaces any standard switch with ease. (Neutral wire required.)

Uses a paddle switch for smoother control with a low-profile aesthetic.

Complete the look with a sleek, screwless wall plate from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Textured	Country Of Origin	China
Features	Smart Lighting, Wireless	Switch Type	Paddle
Number of Switches	1	Works With	Zigbee
Application Sector	Hospitality	Warranty Type	2-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E350248	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Bulb Compatibility	Halogen, Incandescent, LED	Number of Poles	3-Way, Multi-Location, Single Pole
--------------------	----------------------------	-----------------	------------------------------------

Indoor/Outdoor	Indoor	Wattage	1800 W
----------------	--------	---------	--------

Mounting Type	Box	Operating Temperature	0°-40°C
---------------	-----	-----------------------	---------

Voltage	120.0 V
---------	---------
