




radiant Collection  
**radiant® Single Pole 3-Way Occupancy Sensor, Tri-Color**  
Part No. RRW600UTC



Simplify control while saving energy, with the radiant® Occupancy Sensor. Automatically turning the light on when someone enters a room, and shutting it off when the room is empty, this sensor includes an adjustable timed delay for shut off, as well as additional settings for more flexible control. Part of the radiant® Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Passive infrared (PIR) sensor switch technology with 180° coverage up to 600 sq. ft. Rated for up to 600W (5A) of LED lighting.

Turn the light on when you enter, and let it turn itself off automatically after you leave for true convenience. Perfect for bathrooms, hallways, closets, garages, and more.

Features an adjustable time delay to off after no motion is detected. Delay settings range from 30 seconds to 20 minutes after the room is vacated (default 5 minute delay).

Replace any basic light or fan switch in 15 minutes or less. Supports single pole and multi-location installs. No neutral required.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Works with virtually any bulb/fixture, including: LED, incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Auto ON/Auto OFF functionality as default. Easily configurable to Manual ON/Auto OFF to meet any need or preference in the home.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Ivory, Light Almond, White	Country Of Origin	China
Features	Motion Sensor	Switch Type	Motion Sensor
Application Sector	Residential	Standard	cULus

### Dimensions

---

Product Width US	1.69 in	Product Depth US	1.88 in
------------------	---------	------------------	---------

---

Product Height US	2.63 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Target Size	180 deg	Response Frequency	60 Hz
-------------	---------	--------------------	-------

---

Sensor Type	Occupancy	Amperage	5 A
-------------	-----------	----------	-----

---

Number of Poles	3-Way, Single Pole	Wattage	600 W
-----------------	--------------------	---------	-------

---

Mounting Type	Box	Sensing Range	600 sq ft
---------------	-----	---------------	-----------

---

Sensitivity	60Hz	Load	120VAC
-------------	------	------	--------

---

Environmental Conditions	Indoor Use Only
--------------------------	-----------------

---