



radiant Collection

radiant® 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray

Part No. 1597GRYCCD12



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device	Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced
Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected	Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly
Replaces any standard receptacle with ease, in as little as 10 minutes	Features durable, high-impact resistant thermoplastic construction
More color options available to fit any style, including finishes to match current hardware and lighting trends	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Indoor, Residential, Self-Test
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.73 in	Product Depth US	1.25 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2