



Designed for retrofit and new construction, Evolution Series 4" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 2 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Recessed devices: All power devices are recessed below floor level, providing maximum protection and device longevity.

Step-on-it installation: Quick and easy installation without the need for additional fasteners or a second installer.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, [BK] black, [GY] gray, [BZ] bronze, [AL] aluminum, [AA] brushed aluminum, [SB] satin brass, and [SN] satin nickel to seamlessly match your environment.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

Meets ADA accessibility guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Specifications

General Info

Color Silver

UPC Number 786564105084

Countries Of Origin United States

Product Line Wiremold

Application Sector Commercial

Type Poke-Thru

Number of Receptacles 1

Receptacle Type Straight Blade

Standard UL

Number of Knockouts 10

Dimensions

Core Hole Size	4 in
----------------	------

Cubic Capacity	25 cu in
----------------	----------

Additional Information

Product Has Potential to Contribute to LEED	Yes
---	-----

Technical Information

Fire Rating	2 hr
-------------	------

Voltage	125 V
---------	-------

Floor Type	Concrete
------------	----------

Number of Outlets	2
-------------------	---

NEMA Configuration Code	5-20R
-------------------------	-------

Current Rating	20 A
----------------	------

Is Tamper-Resistant	No
---------------------	----
