



Wiremold
4AT Recessed Unwired Poke-Thru Stem Assembly
Part No. 4STC



Designed for retrofit and new construction, Evolution Series 4" Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. 2-gangs of capacity allow you to configure services for the needs of your space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

Features & Benefits

Designed for retrofit and new construction, Evolution Series 4" Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. 2-gangs of capacity allow you to configure services for the needs of your space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

Unique Cover Design: The cover opens a full 180 degrees with sliding doors to keep wires, connections and people safe.

Open System for Expanded Compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

2 Hour Fire Rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

Recessed Devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

6 Finishes: Evolution Series Poke-Thru Devices are available in six finishes to seamlessly match your environment.

Plug Load Control up to 30 Feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564090915
Country Of Origin	United States	Construction	Assembled
Number of Knockouts	10	Application Sector	Commercial

Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes and Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21 300.22[C] and 314 of NEC.	Type	Poke-Thru
----------	---	------	-----------

Dimensions

Product Width US	4.75 in	Product Height US	18.562 in
Cubic Capacity	24.5 cu in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Cable Entry	1 1/2 in trade size conduit for data, 3/4 in trade size conduit for power, .75 in	Number of Outlets	0
-------------	--	-------------------	---