



Wiremold
6AT Prewired AV Evolution™ Poke Thru Device, Surface Style Cover, Gray
Part No. 6ATC2PAVGY



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level – providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

Features & Benefits

Prewired Assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Step-on-it Installation: Quick and easy installation without the need for additional fasteners or a second installer.

Multiple Finishes: Evolution Series Poke-Thru Devices are available in multiple finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass and (SN) satin nickel to seamlessly match your environment.

Surface Style Cover Assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Plug Load Control Up To 30 Feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Meets ADA Accessibility Guidelines. Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

Recessed Devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

Unique Cover Design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

Ideal for High Foot Traffic Environments: Satin brass, satin nickel and brushed aluminum finishes offer a more durable, high-end look with a tougher clear powder coat.

A/V Ready: Plates included to accept industry standard communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

3 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 3 hours, the longest of its type.

UL Listed and UL Fire Classified to U.S. and Canadian safety standards. UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Specifications

General Info

Product Line

Wiremold

Color

Gray

UPC Number	786564088981	Country Of Origin	United States
Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] & 314 of NEC	Type	Poke-Thru
Dimensions			
Product Width US	7.25 in	Product Weight US	10.29 lb
Product Volume US	854.14 cu in	Product Depth US	16.25 in
Product Height US	7.25 in	Cubic Capacity	24.5 cu in
Core Hole Size	6 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Conformant	Yes		
Technical Information			
Cable Entry	Knockouts & Pass Through	Number of Outlets	2