



This dimmer combines the flexibility of Wi-Fi-Lighting Control, with a unique manual control experience that uses a whisper-soft motion to dim and brighten lights. Pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Turn lights on/off or dim with a whisper-soft motion; or create custom lighting scenes lights through the Legrand Lighting Control app for your smartphone or tablet. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. A Tru-Universal Dimmer, this device works with virtually any 120V dimmable bulb or fixture. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

- Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.
- Pair with a Whisper Wi-Fi Ready Remote Dimmer for 3-way control.
- Works with virtually any 120V dimmable bulb or fixture.
- Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.
- Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.
- Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.
- Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

## Specifications

### General Info

|                   |   |                    |                                  |
|-------------------|---|--------------------|----------------------------------|
| Product Line      | Pass & Seymour                                  | Color              | Graphite                         |
| Country Of Origin | China   | Features           | Indicator Lights, Smart Lighting |
| Switch Type       | Whisper   | Number of Switches | 1                                |
| Works With        | Amazon Alexa, Google Assistant, Radio Frequency | Warranty Type      | Limited Lifetime Warranty        |

Technical Information

|                    |   |                 |                                    |
|--------------------|---|-----------------|------------------------------------|
| Electrical Rating  | 120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL) | Number of Gangs | 1                                  |
| Bulb Compatibility | CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon   | Number of Poles | 4-Way, Multi-Location, Single Pole |
| Wattage            | 700 W   | Mounting Type   | Box                                |
| Voltage            | 120 V   | Connection Type | Internal Pressure Plates           |