




radiant Collection  
radiant 65W USB Outlet, Type C, 15A, Tamper-Resistant, Brown  
Part No. EWS\_PS\_R26USBPD65



Charge the latest smartphones, tablets and small laptops with the 65W USB Outlet featuring dual Type-C USB ports with Power Delivery. The result is a fast, long-lasting outlet for convenient in-wall charging, specially designed to safely and efficiently charge your devices. Easily replace a traditional outlet in as little as ten minutes to gain the modern functionality of intelligent charging for maximized speeds, complete with multi-layered overcurrent protection to keep the outlet and your devices safe from damage. An industry-exclusive charging indicator light tells you when your device is charging and when it's fully charged, for life on the go. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Charges the latest electronics, including small laptops like the 13-in MacBook Pro, Chromebooks, and Microsoft Surface Pro 9 thanks to industry-leading amperage and 65W of power courtesy of advanced Power Delivery

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds

Provides fast and convenient built-in charging through two USB Type-C ports, accommodating modern devices without an adapter

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is 90% charged

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Limited Lifetime Warranty

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Simple and easy to wire lead reduces installation time

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007456271	Number of Receptacles	2
Features	Indicator Lights, USB-C Charging	Outlet Type	Tamper-Resistant, USB

---

Application Sector	Hospitality, Residential	Wall Plate Included	No
--------------------	--------------------------	---------------------	----

---

Standard	cULus, UL	Warranty Type	Limited Lifetime Warranty
----------	-----------	---------------	---------------------------

---

### Dimensions

---

Product Width US	2.99 in	Product Weight US	0.42 lb
------------------	---------	-------------------	---------

---

Product Depth US	1.52 in	Product Height US	1.94 in
------------------	---------	-------------------	---------

---

Product Length US	4.88 in		
-------------------	---------	--	--

---

### Additional Information

---

RoHS Compliant	Yes		
----------------	-----	--	--

---

### Technical Information

---

Operating Temperature Min	-40 °C	USB Wattage	65 W
---------------------------	--------	-------------	------

---

Number of USBs	2	Number of Wires	3
----------------	---	-----------------	---

---

Operating Temperature Max	60 °C	Amperage	15 A
---------------------------	-------	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

NEMA Configuration Code	5-15R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

---

Wire Connection Type	Wire Leads	Voltage	15.0 V, 5.0 V, 9.0 V
----------------------	------------	---------	----------------------

---