



**Wattstopper**  
**Discontinued - PIR Multi-way Wall Switch Sensor w/nightlight White**  
Part No. PW-103N-W



The PW-103N passive infrared (PIR) multi-way wall switch sensor can turn lights OFF and ON based on occupancy. It provides high sensitivity to small and large movements, appealing aesthetics, a field selectable nightlight and a variety of features.

## Features & Benefits

Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI	Defaults to Manual-ON operation for maximum energy savings
Vandal resistant lens combines precise coverage with durability	In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations
Choice of Manual-ON or Auto-ON operation	Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds
Selectable audible and/or visual alerts for impending shutoff	2-wire and 3-wire models available for applications with or without neutral wire
High sensitivity and dense coverage for exceptional performance	Color-matched lens and low profile for appealing design
Optional nightlight with choice of three colors and two light levels	Allows multi-way control from one of up to four control locations
Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience	High sensitivity and dense coverage for exceptional performance
Optional nightlight with choice of three colors and two light levels	Color-matched lens and low profile for appealing design
Allows multi-way control from one of up to four control locations	Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience
Defaults to Manual-ON operation for maximum energy savings	

## Specifications

### General Info

Product Line	Wattstopper	Replaced by Part Number	RS-150BA-N-W
Color	White	UPC Number	754182928590
Country Of Origin	China	Features	IR (Infrared), Motion Sensor, Nightlight
Switch Type	Motion Sensor	Application Sector	Commercial
Warranty Type	5-Year		

### Dimensions

Product Width US	2.0 in	Product Weight US	0.35 lb
Product Volume US	27.6 cu in	Product Depth US	2.75 in
Product Height US	4.48 in		

### Additional Information

RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes	Product Environmental Profile	Yes

### Technical Information

Response Frequency	50/60 Hz	Sensor Type	Occupancy
Number of Buttons	1	Amperage	4.3 A
Indicator	LED Light	Wattage	1200 W
Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Voltage	120/277 V
Connection Type	Wired		