



**Wattstopper**  
**Wattstopper PLUS Wireless Zone Control WallStation, 3 Button, Ivory**  
Part No. BCS\_WA\_EN-WS-ZC3-ZB-IV



The ZC Zone Controller Wallstation series is a multi-zone Wallstation that offers software configurable lighting control that provides ON/OFF switching for multiple lighting zones. It is generally located at entry points to a floor or department and is used to activate or deactivate a lighting zone. The zone status is indicated by an LED display with white indicating ON and blue indicating OFF.

## Features & Benefits

The sleek, aesthetic designs are suitable for all interior locations

Setup and monitoring via Polaris software with easy mapping/re-mapping

10-year battery life for wireless version with automatic battery monitoring via Polaris software

## Specifications

### General Info

Product Line	Wattstopper	Color	Ivory
Finish	Plastic	UPC Number	840356702254
Country Of Origin	Canada	Switch Type	Push
Number of Switches	3	Application Sector	Commercial
Warranty Type	5-Year	Type	Switch

### Dimensions

Product Width US	2.76 in	Product Weight US	0.35 lb
Product Depth US	0.94 in	Product Height US	4.5 in

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

---

cUL Listed	Yes
------------	-----

---

### Additional Information

---

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

---

### Technical Information

---

Operating Temperature Min	-10 °C	Compatibility	Wattstopper PLUS Wireless, Zigbee
---------------------------	--------	---------------	-----------------------------------

---

Has Battery	Yes	Number of Connections	0
-------------	-----	-----------------------	---

---

Battery Capacity	3 V	Frequency Band	2.4 GHz
------------------	-----	----------------	---------

---

Operating Temperature Max	40 °C	Number of Buttons	3
---------------------------	-------	-------------------	---

---

Number of Rockers	0	Wireless Range	Zigbee, up to 100 ft
-------------------	---	----------------	----------------------

---

Antenna	Integrated, Internal	Input Voltage	3 VDC
---------	----------------------	---------------	-------

---

Indoor/Outdoor	Indoor	Battery Life	Up to 10 Years
----------------	--------	--------------	----------------

---

Mounting Type	Surface	Battery	2 AA
---------------	---------	---------	------

---

Operating Temperature	-10°-40°C, 14°-104°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	----------------------	--------------------	---------------------------

---

Wire Connection Type	Wireless	Antenna Pattern	Omni-directional
----------------------	----------	-----------------	------------------

---

Engraving Type	Icon
----------------	------

---