




radiant Collection  
radiant® Easy Switched Outlet Kit, White  
Part No. WNREZK15WH



This kit uses a wireless switch to easily add on-wall control of an outlet, then simply flip the switch to control a plugged-in lamp or small appliance.

To start, replace an existing outlet with the kit's radiant® 15A Outlet (wired). Then use the included battery-powered radiant® Wireless Switch to add on-wall control wherever it is desired. The Wireless Switch mounts to any wall or surface – without cutting, wiring or tools – using the provided adhesive. The devices come pre-paired, letting you add switch control in seconds.

Want app control? These devices are equipped for enhanced functionality. Simply add a Smart Gateway with Netatmo and use the Legrand Home + Away app to control your lights from anywhere (and much more). For more information visit [www.legrand.us/addappcontrol](http://www.legrand.us/addappcontrol). Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Easily adds on-wall control of lamps or small appliances.

Ready to install, no configuration needed.

Outlet (Wired) Installation: Replaces any standard (wired) outlet in as little as 15 minutes.

Switch (Wireless) Installation: Mounts to any wall for long-lasting, battery-powered control.

One outlet is switch controlled, the other is always on.

Add a Smart Gateway with Netatmo to control lights via app, connect to other smart products and more.

Screwless Wall Plates included. Coordinate with other designer switches and outlets from the radiant® Collection for a cohesive, sophisticated look.

## Specifications

### General Info

|                   |                  |                    |                        |
|-------------------|------------------|--------------------|------------------------|
| Product Line      | Pass & Seymour   | Color              | White                  |
| Finish            | Matte            | UPC Number         | 785007442694           |
| Country Of Origin | China            | Number of Switches | 1                      |
| Works With        | Netatmo          | Application Sector | Residential/Commercial |
| Standard          | RoHS, FCC, cULus | Warranty Type      | 1-Year                 |

---

|      |                          |
|------|--------------------------|
| Type | Duplex, Tamper-Resistant |
|------|--------------------------|

---

### Listing Agencies / 3rd Party Agencies

---

|              |     |                      |     |
|--------------|-----|----------------------|-----|
| cULus Listed | Yes | Regulatory Approvals | Yes |
|--------------|-----|----------------------|-----|

---

|               |     |
|---------------|-----|
| FCC Compliant | Yes |
|---------------|-----|

---

### Additional Information

---

|                 |     |   |     |
|-----------------|-----|---|-----|
| RoHS Conformant | Yes | Product Has Potential to Contribute to LEED | Yes |
|-----------------|-----|---|-----|

---

### Technical Information

---

|            |                 |          |      |
|------------|-----------------|----------|------|
| Connection | Wireless, Wired | Amperage | 15 A |
|------------|-----------------|----------|------|

---

|                |        |         |         |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 120.0 V |
|----------------|--------|---------|---------|

---

|                          |   |
|--------------------------|---|
| Environmental Conditions | 95% (relative humidity, non-condensing) |
|--------------------------|---|

---