

Pass and Seymour Hospital Grade Amber Power-Indicating LED Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, White Part No. 2097HGTRPIAMBW

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection - if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Visual LED power identification of receptacles to ensure proper functionality for necessary loads. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Power Indicating Green LED flashes if the device needs to be replaced

Tamper-Resistant automatic shutter system prevents insertion. Black shutters essentially ""disappear"" into the background for an invisible effect preferred by end users

Two back-wire holes per termination add wiring flexibility, eliminate pigtailing and save box space

Ground terminal back-wire for fast installation

FSUL Listed (Federal Specification WC596)

Hospital Grade GFCI specially designed and tested for rigorous healthcare applications

The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced

High-impact-resistant, thermoplastic construction for superior strength and durability

Auto-ground clip assures a positive ground to metal box

Specifications

General Info			
Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	Indicator Lights
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper- Resistant	Warranty Type	1-Year Limited Warranty
Туре	Duplex, GFCI, Tamper-Resistant, USB		
Dimensions			
Product Width US	1.32 in	Product Depth US	0.833 in
Product Height US	3.81 in		
Additional Information			
RoHS Conformant	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Number of Gangs	1
Amperage	20 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Вох
Voltage	125.0 V		