

radiant Collection radiant® Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Type A/C Outlet, Graphite Part No. 2097TRUSBACGC4



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere	Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports	Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
	Protect children using a patented "'invisi-shutter" system to prevent the insertion of r foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper- Resistant requirements
Installs quickly thanks to a redesigned side wire cavity for easier access	Can provide ground fault protection to downstream outlets through feed-thru wiring
Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection	5

Specifications

General Info

Product LinePass & SeymourColorGraphiteFinishMetallicCountry Of OriginChinaNumber of Receptacles2FeaturesUSB-A Charging, USB-C ChargingOutlet TypeGFCI, Indoor, Residential, Self-Test, Tamper- Resistant, USB-ChargingWarranty Type1-Year Limited WarrantyTypeOutletUtletIndoceIndoceProduct Width US1.73 inProduct Depth US1.03 inProduct Height US4.2 inIndoceIndoce				
Number of Receptacles2FeaturesUSB-A Charging, USB-C ChargingOutlet TypeGFCl, Indoor, Residential, Self-Test, Tamper- Resistant, USB-ChargingWarranty Type1-Year Limited WarrantyTypeOutletOutletDimensionsProduct Width US1.73 inProduct Depth US1.03 in	Product Line	Pass & Seymour	Color	Graphite
Outlet TypeGFCl, Indoor, Residential, Self-Test, Tamper- Resistant, USB-ChargingWarranty Type1-Year Limited WarrantyTypeOutletDimensionsProduct Width US1.73 inProduct Depth US1.03 in	Finish	Metallic	Country Of Origin	China
Outlet Type Resistant, USB-Charging Warranty Type T-Year Limited Warranty Type Outlet Outlet Image: Charging Dimensions Image: Charging Image: Charging Product Width US 1.73 in Product Depth US 1.03 in	Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Dimensions Product Width US 1.73 in Product Depth US 1.03 in	Outlet Type		Warranty Type	1-Year Limited Warranty
Product Width US 1.73 in Product Depth US 1.03 in	Туре	Outlet		
	Dimensions			
Product Height US 4.2 in	Product Width US	1.73 in	Product Depth US	1.03 in
	Product Height US	4.2 in		

Is Tamper-Resistant	Yes	USB Amperage	2.1 A
Number of USBs	2	Number of Gangs	1
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Wattage	1875 W
Mounting Type	Box	Voltage	125.0 V