



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant Weather-Resistant Duplex Receptacle, White  
Part No. 3232TRWRW



15A/125A Weather-Resistant Duplex Receptacle,

## Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Outdoor, Residential, Tamper-Resistant, Weather-Resistant
Application Sector	Residential/Commercial	Standard	UL 498
Type	Outlet		

### Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

Product Environmental Profile    Yes

---

## Technical Information

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	4 AWG	Indoor/Outdoor	Outdoor
-----------	-------	----------------	---------

---

Voltage	125.0 V		
---------	---------	--	--

---