



Pass and Seymour
Commercial Specification Grade Switch, Light Almond
Part No. CS20AC3LA



Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2
Type	Switch		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	One piece brass alloy contact arm	Actuator	Toggle
-----------------------	-----------------------------------	----------	--------

Connection	Side Wire or external screw-pressure plate	Contact Rating	Oversized silver alloy contacts
------------	--	----------------	---------------------------------

Amperage	20 A	Number of Poles	3-Way
----------	------	-----------------	-------

Indoor/Outdoor	Indoor	Operating Temperature	-40°-115°C
----------------	--------	-----------------------	------------

Voltage	120/277 V	Connection Type	Wired
---------	-----------	-----------------	-------

Degree of Protection	1500V Dielectric Withstand Voltage
----------------------	------------------------------------
