




Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



## Features & Benefits

|   |  |
|---|--|
| Unique Key and Color Options: Up to thirteen unique keying options/colors for a wide range of network security systems, easy identification and network management          | Keyed front or Rear: Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirement                    |
| Compatibility: All Legrand keyed LC fiber products are engineered to be compatible with other Legrand products to provide an end to end, data center to desktop solution.   | Various Footprint Options: Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility. |
| Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility. | Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirements.                                       |

## Specifications

### General Info

|                   |           |            |              |
|-------------------|-----------|------------|--------------|
| Product Line      | Ortronics | UPC Number | 662875029250 |
| Country Of Origin | Mexico    | Type       | Adapter      |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 0.62 in | Product Depth US | 1.61 in |
| Product Height US | 0.77 in |                  |         |

### Technical Information

|               |                                    |                    |             |
|---------------|------------------------------------|--------------------|-------------|
| Compatibility | HDJ, PHDHJU                        | Temperature Rating | 20° - 75° C |
| Adapter Color | Yellow                             | Connector Type     | LC Duplex   |
| Repeatability | < 0.2dB typical change,500 matings | Adapter Rear       | Keyed       |
| Adapter Front | Keyed                              |                    |             |