



Pass and Seymour Plug-In Home Level 2 EV Charger

Part No. L2EVSE40ACP1450



Compact yet powerful, the Plug-In Home Level 2 EV Charger is the safe, easy and efficient way to charge any electric vehicle at home. Designed for indoor or outdoor use, simply plug the unit in for Level 2 charging in garages or driveways. The charger comes ready-to-use right out of the box and requires no internet connection or software. An Energy Star-certified product, this Level 2 EV Charger is eligible for rebates and incentives in select states.

Features & Benefits

Ready-to-use unit comes preassembled with flexible cord whip and NEMA 1450 plug.

Delivers fast level 2 charging: charges from 0 to 100% in 8-10 hours and can provide up to a 38-mile range per hour of charging.

Sleek and compact, the unit simply plugs in – indoors or out – for easy charging in garages, driveways or carports.

Works with any* electric vehicle using a SAE J1772 Connector, the North American standard for EV charging. *Adapter required for Tesla models.

Indicates charging status via LED light, easily showing if the vehicle is charging, fully charged or if there is a charging issue, all at a glance.

Features an 18-foot charging cable for easily reaching multiple parking spots.

Includes storage hook and holster for keeping the charging cable neatly off the floor for both safety and convenience.

Meets the efficiency standards required by the Energy Star program, qualifying users for potential rebates and tax credits. Visit www.energystar.gov for eligibility details.

Meets Safety & Materials Standards: cETLus listed to UL standards, FCC & ID certified, and CA Prop-65 and RoHS compliant.

Power Deliver: 9.6 KW @40A

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Application Sector	Residential	Standard	cETLus, FCC, IC, Energy Star, CA Prop 65, RoHS

Warranty Type	1-Year Limited Warranty	Type	Charging Stations
---------------	-------------------------	------	-------------------

Dimensions

Product Width US	3.7 in	Product Weight US	15.0 lb
Product Depth US	3.7 in	Product Height US	7.1 in
Product Length US	7.1 in	Cable Length	18 ft

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes	FCC Compliant	Yes
------------	-----	---------------	-----

Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----

Technical Information

Connection	SAE J1772 Connector (North America Standard)	Amperage	40 A
Enclosure Type	NEMA 3R	Indoor/Outdoor	Both
Wattage	9600 W	NEMA Configuration Code	NEMA 14-50
Mounting Type	Pedestal	Adapter Front	SAE J1772
Power Delivery	9.6 KW	Voltage	208/240 V
Connection Type	Hardwired, Plug-In	Environmental Conditions	95% (relative humidity, non-condensing)
