



Pass and Seymour
Fusible Safety Switch, 60As
Part No. PS60FSS



Fusible Safety Switch, 60 Amps, 600 VAC. The first-ever blown-fuse indication system that's in our pacesetter Fusible Mechanical Interlocks with individual LED indicators for each line, patent-pending integral fuse pullers, and a hinged fuse-access door. Pass and Seymour Fusible Safety Switches deliver the same ultra-heavy-duty construction as our Fusible Mechanical Interlocks, too. So they provide maximum protection against water, dirt, heat, and vibration and just about any other harsh condition you'll encounter.

Features & Benefits

Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.

Captive, quick-release, stainless steel screws speed fuse removal, ensure a watertight access door seal, and won't fall out.

Heavy-duty steel-gear switch mechanism provides enhanced durability and extra-long service life.

Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle.

Durable, stainless steel cover-retaining chain makes installation and maintenance more convenient.

Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.

Time-saving LED indicators identify blown fuses at a glance.

Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout requirements and provides plenty of grip for sure, easy operation.

Separate door for ease of changing fuses.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Amperage

60 A

Number of Poles

4-Way

Voltage

600.0 V
