



**Wattstopper**  
**PIR Wall Switch Occupancy Sensor, 120/277V, Lt Almond**  
Part No. PW-302-LA



The PW-302 passive infrared (PIR) wall switch sensor turns lights ON and OFF based on occupancy. It contains two relays for controlling two independent lighting loads or circuits, and a variety of features.

## Features & Benefits

High sensitivity and dense coverage for exceptional performance

Two relays for control of two separate lighting loads or circuits

Defaults to Auto-ON to 50% operation for maximum energy savings

Optional neutral connection with break off tab to expose neutral terminals

120/240/277 VAC and 347 VAC models

Allows multi-way control from one of up to four control locations

Allows multi-way control from one of up to four control locations

## Specifications

### General Info

Product Line	Wattstopper	Color	Light Almond
--------------	-------------	-------	--------------

UPC Number	754182935307	Country Of Origin	China
------------	--------------	-------------------	-------

Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
----------	------------------------------	-------------	---------------

Application Sector	Commercial
--------------------	------------

### Dimensions

Product Width US	2.0 in	Product Weight US	0.47 lb
------------------	--------	-------------------	---------

Product Volume US	35.02 cu in	Product Depth US	2.99 in
-------------------	-------------	------------------	---------

---

Product Height US	4.8 in
-------------------	--------

---

### Additional Information

---

RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
-----------------	-----	--	-----

---

Security	Yes
----------	-----

---

### Technical Information

---

Response Frequency	50/60 Hz	Sensor Type	Occupancy
--------------------	----------	-------------	-----------

---

Number of Buttons	2	Amperage	4.3 A
-------------------	---	----------	-------

---

Wattage	1200 W	Mounting Type	Box
---------	--------	---------------	-----

---

Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
---------------	-------------------------	---------	-----------

---

Connection Type	Wired	Load	800W
-----------------	-------	------	------

---