

# radiant Collection radiant® 2-Wire Fluorescent Dimmer, Tri-Color

Part No. RHFB83PTC



Upgrade your space with precise dimming and exceptional style. This dimmer is designed for use with 2-wire fluorescent fixtures, and features the clean lines and smooth control of the radiant® Collection. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

### Features & Benefits

Replaces any basic switch or dimmer with ease, in both single-pole and 3-way applications. For use with 2-wire fluorescent lighting fixtures.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating\* required for 2-gang applications. \*Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

#### General Info Product Line Color Pass & Seymour Ivory, Light Almond, White Country Of Origin China Switch Type Paddle Number of Switches Residential Application Sector Standard CSA Listed, cULus, UL Listed Warranty Type Limited Lifetime Warranty Dimmer Type

## **Dimensions**

Product Width US	2.5 in	Product Depth US	1.25 in
Product Height US	4.25 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Number of Gangs	1	Amperage	15 A
Bulb Compatibility	Fluorescent	Number of Poles	3-Way, Single Pole
Mounting Type	Вох	Voltage	120.0 V
Load	Fluorescent	Environmental Conditions	Humidity: Less than 95% non condensing