



Pass and Seymour  
15A 125V Fed Spec-Grade Tamper-Resistant USB Type A/A Outlet, Ivory  
Part No. TR5262USBI



Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices. Auto-ground clip assures positive ground.
  - AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. Multiple color options available.
  - Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.
- Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                    |                         |                       |  |
|--------------------|-------------------------|-----------------------|--|
| Product Line       | Pass & Seymour          | Color                 | Ivory  |
| Country Of Origin  | China                   | Number of Receptacles | 2  |
| Features           | USB-A Charging          | Outlet Type           | Commercial, Indoor, Tamper-Resistant, USB-Charging |
| Application Sector | Commercial              | Standard              | CSA Listed, cULus, FSUL, UL Listed, RoHS           |
| Warranty Type      | 1-Year Limited Warranty | Type                  | Outlet   |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.693 in | Product Depth US | 1.392 in |
| Product Height US | 2.677 in |                  |          |

### Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

### Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

### Technical Information

---

|                     |                          |                     |     |
|---------------------|--------------------------|---------------------|-----|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
|---------------------|--------------------------|---------------------|-----|

---

|              |       |       |        |
|--------------|-------|-------|--------|
| USB Amperage | 3.1 A | Phase | Single |
|--------------|-------|-------|--------|

---

|            |                   |                |   |
|------------|-------------------|----------------|---|
| Connection | Side & Back Wired | Number of USBs | 2 |
|------------|-------------------|----------------|---|

---

|                 |   |                  |      |
|-----------------|---|------------------|------|
| Number of Wires | 3 | USB Power Output | 15 W |
|-----------------|---|------------------|------|

---

|                    |              |          |      |
|--------------------|--------------|----------|------|
| Temperature Rating | -40° - 60° C | Amperage | 15 A |
|--------------------|--------------|----------|------|

---

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

---

|                |        |         |         |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
|----------------|--------|---------|---------|

---

|                          |         |
|--------------------------|---------|
| Environmental Conditions | UL94 V2 |
|--------------------------|---------|

---