



Pass and Seymour  
Turnlok® SteriGuard™ Antimicrobial Plug 30A, 125V  
Part No. 28W47AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

## Features & Benefits

|  |   |
|--|---|
| UL and CSA Listed  | NSF (National Sanitation Foundation) Certified  |
| Patent Pending   | Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi  |
| Anti-microbial Additive Resistant to Scuffing and Cleaning   | Escherichia (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99% |
| Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%  | Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%            |
| RoHS Compliant (Non-Halogenated)   | Independently tested and Certified to JIS Z2801 standards   |
| Resistant to High Pressure Hose-down applications  | Tongue & Groove Environmental Sealing   |
| Keyed Body and Cover for Alignment   | NEMA Type 4, 4x, 6, 6P and IP67 Protection  |
| Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care. |   |

## Specifications

### General Info

|                   |                |          |                       |
|-------------------|----------------|----------|-----------------------|
| Product Line      | Pass & Seymour | Color    | Yellow                |
| Country Of Origin | United States  | Standard | UL Listed, CSA Listed |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.85 in | Product Depth US | 2.62 in |
| Product Height US | 1.85 in |                  |         |

Technical Information

|                          |  |                 |             |
|--------------------------|--|-----------------|-------------|
| Phase                    | Single   | Number of Wires | 3           |
| Amperage                 | 30 A   | Number of Poles | Double Pole |
| Wire Size                | 14 - 10 AWG  | Voltage         | 125.0 V     |
| Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |                 |             |