

Receptacle Single 15A 250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Industrial | Standard | UL 498 |

Dimensions

| | | | |
|------------------|----------|-------------------|----------|
| Product Depth US | 0.922 in | Product Height US | 2.375 in |
|------------------|----------|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | NO | | |

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-------|--------------|-----------------|---|
| Phase | Single-Phase | Number of Wires | 3 |
|-------|--------------|-----------------|---|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|------------|---------|---------|
| Wire Size | 18 - 0 AWG | Voltage | 250.0 V |
|-----------|------------|---------|---------|
