



Clarity SNAP™ Terminated Copper Cabling System offers the above-the-standards performance of Clarity® connectivity in a custom terminated cable assembly system that's ready to plug and go. Its innovative modular design combines high performance and installer friendly features with the quick deployment and reliability of a factory terminated and tested cabling system.

Features & Benefits

Totally modular cabling system: Dramatically faster deployment of horizontal cabling and port replication

Factory-installed and tested terminations: Assembled in a controlled factory environment for consistent performance to elevated requirements confirmed by factory testing. Factory tested terminations reduce the time and cost of field testing

Reduced size of cable ends: Easier cable pulling and directing through pathways and racks

Clarity® 6A/10G, 6 and 5E performance: Premium performance you've come to rely on from Clarity connectivity, now in a terminated solution

Factory supplied identification: Each cable assembly includes part number and unique identifiers for traceability and association to its factory test report

Variety of options: Solutions tailored to your specific needs

Increased flexibility for MACs: Reduces total cost of ownership and allows re-use in the future (also reducing waste)

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875838111	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Patch Cable		

Dimensions

Product Length US	75.0 FT	Cable Length	75 ft
-------------------	---------	--------------	-------

Technical Information

Category Performance Rating	Cat 6a	Storage Humidity	0-100% RH (Non-Condensing)
-----------------------------	--------	------------------	----------------------------

Plating Specification	50 μ in Gold	Bend Radius	0.94 in
-----------------------	------------------	-------------	---------

Cable Type	Ethernet Patch Cable	Jacket Rating	LSZH
------------	----------------------	---------------	------

Amperage	0.96 A	Cable Diameter	0.236 in
----------	--------	----------------	----------

Wattage	100 W	Operating Humidity	0-100% RH (Non-Condensing)
---------	-------	--------------------	----------------------------

Conductor Material	Copper	Voltage	57.0 V
--------------------	--------	---------	--------
