



PlugTail® Spec Grade Receptacles, 20A, 125V. These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

| | |
|---|--|
| .032 inch thick, brass, triple-wipe power contacts for lasting retention. | Large brass contacts snugly terminate on device blade terminals. |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. |
| Dual mechanical shutter system to help prevent insertion of foreign objects (TR models). | Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC. |
| Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications. | For covering patents, see www.legrand.us/patents . |
| For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . | |

Specifications

General Info

| | | | |
|-------------------|--|-----------------------|--------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Energy Saving On/Off, Indoor | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|----------------|--------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |