



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- .032 inch thick, brass, triple-wipe power contacts for lasting retention. Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Dual mechanical shutter system to help prevent insertion of foreign objects (TR models). Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.
- Auto-ground clip assures positive ground. Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.
- For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).
- Wire Size: #12 AWG THHN

Specifications

General Info

| | | | |
|-------------------|-----------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL Listed, CSA Listed, FSUL | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------------|--------------------------|---------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Phase | Single | Connection | PlugTail |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 12 AWG | Voltage | 125.0 V |
| Environmental Conditions | UL94 V2 | | |
