



## Legrand

PlugTail® Tamper-Resistant Heavy-Duty Spec Grade Plug Load Controllable Receptacle, 20A, 125V, Black  
Part No. PTTR5362CDBK



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Dual mechanical shutter system to help prevent insertion of foreign objects (TR models).	Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.
Auto-ground clip assures positive ground.	Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .

### Specifications

#### General Info

Color	Black
UPC Number	785007051667
Countries Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	UL Listed, CSA Listed, FSUL

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Number of Poles	Double Pole
Voltage	125 V
Connection	PlugTail

---

<b>Dielectric Strength</b>	Withstands 2000V minimum
<b>Phase</b>	Single
<b>Temperature Rating</b>	Maximum continuous +60°C, minimum -40° without impact
<b>Wire Size</b>	#12 AWG THHN
<b>Number of Wires</b>	3
<b>Environmental Conditions</b>	UL94 V2

---