



Wattstopper  
Digital PIR Corner Mount Sensor, 1-sided aisle, USA  
Part No. LMPX-100-4-U



The LMPX-100 Digital PIR Corner Mount Occupancy Sensor uses passive infrared (PIR) technology and one of four lenses to detect occupancy in different types of spaces for energyefficient control of lighting and plug loads. It is a digital sensor, and is part of a Wattstopper Digital Lighting Management (DLM) system.

## Features & Benefits

Passive infrared sensor with a choice of four coverage patterns

Quick access to Push n' Learn for system personalization

IR transceiver for wireless configuration and remote control

High density, long range and aisle lenses

Component of Digital Lighting Management integrated control system

Digital sensor with LCD display and programming pushbuttons behind snap-down cover

Compact 2.4" x 3" sensor mounts easily on a wall or ceiling

## Specifications

### General Info

Product Line	Wattstopper	Color	White
UPC Number	754182927593	Country Of Origin	United States
Product Series	LMPX-100	Features	Adjustable Time Delay, Indicator Lights, Room Controller Required, Sensitivity Adjustment
Installation Location	Ceiling, Wall	Included	RJ-45 Coupler
Standard	UL, cUL, FCC part 15, RoHS, PEP, BAA, TAA	Warranty Type	5-Year
Type	Sensor		

---

## Dimensions

---

Product Width US	2.5 in	Product Weight US	0.3 lb
Product Volume US	117.0 cu in	Product Depth US	3.8 in
Product Height US	3.0 in		

---

## Technical Information

---

Operating Temperature Min	32 °F	Has Battery	No
Number of Connections	1	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	10 ft
Sensor Technology	Passive Infrared (PIR)	Topology	Free Topology
Input Voltage	24 VDC	Indoor/Outdoor	Indoor
Sensor Coverage	50 ft	Mounting Type	Ceiling Tile, J-Box, Surface
On Function	Auto On	Current Draw	7 mA
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	6 x 50 ft	Wire Connection Type	RJ-45
Storage Temperature	23° - 176° F, -5° - 80° C		

---