



The PW-302 passive infrared (PIR) wall switch sensor turns lights ON and OFF based on occupancy.

## Features & Benefits

Defaults to Auto-ON to 50% operation for maximum energy savings

120/240/277 VAC and 347 VAC models

High sensitivity and dense coverage for exceptional performance

Optional neutral connection with break off tab to expose neutral terminals

Allows multi-way control from one of up to four control locations

Two relays for control of two separate lighting loads or circuits

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
Application Sector	Commercial		

### Dimensions

Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in

### Technical Information

Response Frequency	60 Hz	Sensor Type	Occupancy
Number of Buttons	2	Indoor/Outdoor	Indoor
Wattage	1200 W	Mounting Type	Box
Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
Connection Type	Wired	Load	800W