



Pass and Seymour  
PlugTail® Isolated Ground Spec Grade Receptacles, 20A, 125V, White  
Part No. PTIG5362W



PlugTail® Isolated Ground Spec Grade Duplex Receptacle 20 A 125 V

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		

### Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	12 AWG
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2