



Wattstopper
Wattstopper PLUS GreenBus Wallstation, 4 Button, Ivory
Part No. BCS_WA_EN-WS-4B-GB2-IV



The WS Standard Wallstation Series consists of a two-button and a four-button wallstation that enable essential lighting control. The 2-button wallstation is a single zone manual controller ideal for conference rooms, private offices, classrooms, and other similar spaces. A short press of the upper/ lower buttons turns lighting ON/OFF, while a "press and hold" dim lighting up or down. The 4-button wallstation is a single zone manual controller ideal for conference rooms, libraries, and other similar spaces. It has a dedicated button for ON, OFF, and for raise/lower functionality with intuitive button engraving. The WS Standard Series Wallstations are available in wired and wireless options.

Features & Benefits

The sleek, aesthetic designs are suitable for all interior locations

Setup and monitoring via Polaris software with easy mapping/re-mapping

LED indicator for ON/OFF feedback

Specifications

General Info

Product Line	Wattstopper	Color	Ivory
Finish	Plastic	UPC Number	840356701905
Country Of Origin	Canada	Switch Type	Push
Number of Switches	4	Application Sector	Commercial
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	2.76 in	Product Weight US	0.2 lb
Product Depth US	0.94 in	Product Height US	4.5 in

Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes	cUL Listed	Yes
---------------	-----	------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---------------------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Has Battery	No
---------------------------	--------	-------------	----

Operating Temperature Max	40 °C	Number of Buttons	4
---------------------------	-------	-------------------	---

Number of Rockers	0	Input Voltage	24 V
-------------------	---	---------------	------

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

Operating Temperature	-10°-40°C	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	-----------	--------------------	------------------------------

Wire Connection Type	GreenBus	Engraving Type	Icon with Text
----------------------	----------	----------------	----------------
