



## Wattstopper DLM Low Voltage 1-Button Shade Wall Switch

Part No. BCS\_WA\_LMSH-SW101LA



Legrand's series wall switches are low voltage device for manual control of shades in one or more locations. This device has 1 or more buttons and can control any shade motors connected to DLM shade controllers. The switches connect using standard DLM IRB RJ45 cables and have a counter balanced design that allows shades to be pulled into position from the hembar.

### Features & Benefits

Available in four different switch configurations to support control of any shade project

Available in six color options: White, Black, Grey, Ivory, Light Almond and Red

Switches are pre-engraved with most common control configurations

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Customizable buttons with LED status indicators

Matches DLM Lighting Control switches for consistent design of lighting and shade control

Includes system configuration button for easy system programming from the switch

IR transceiver for wireless configuration and remote control

Components of Digital Lighting Management integrated shade control system

Custom engraving or engraved and non-engraved button kits available

### Specifications

#### General Info

Product Line	Wattstopper	Color	Light Almond
UPC Number	842854000276	Country Of Origin	China
Product Series	LMSW-SH	Number of Switches	1
Application Sector	Commercial	Warranty Type	Lifetime
Type	Switch		

#### Dimensions

Product Width US	1.8 in	Product Weight US	0.15 lb
Product Volume US	22.8 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

### Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes	cUL Listed	Yes
---------------	-----	------------	-----

### Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

### Technical Information

Operating Temperature Min	0 °C	Has Battery	No
Operating Temperature Max	55 °C	Number of Buttons	0
Number of Rockers	1	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Current Draw	5 mA
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	RJ-45	Engraving Type	Icon