



Wattstopper
DLM Low Voltage 2-Button Shade Wall Switch
Part No. BCS_WA_LMSH-SW102G



Legrand's series wall switches are low voltage device for manual control of shades in one or more locations. This device has 1 or more buttons and can control any shade motors connected to DLM shade controllers. The switches connect using standard DLM IRB RJ45 cables and have a counter balanced design that allows shades to be pulled into position from the hembar.

Features & Benefits

Available in four different switch configurations to support control of any shade project

Available in six color options: White, Black, Grey, Ivory, Light Almond and Red

Switches are pre-engraved with most common control configurations

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Customizable buttons with LED status indicators

Matches DLM Lighting Control switches for consistent design of lighting and shade control

Includes system configuration button for easy system programming from the switch

IR transceiver for wireless configuration and remote control

Components of Digital Lighting Management integrated shade control system

Custom engraving or engraved and non-engraved button kits available

Specifications

General Info

| | | | |
|----------------|--------------|--------------------|------------|
| Product Line | Wattstopper | Color | Green |
| UPC Number | 842854000320 | Country Of Origin | China |
| Product Series | LMSW-SH | Application Sector | Commercial |
| Warranty Type | Lifetime | Type | Switch |

Dimensions

| | | | |
|-------------------|------------|-------------------|---------|
| Product Width US | 1.8 in | Product Weight US | 0.15 lb |
| Product Volume US | 22.8 cu in | Product Depth US | 1.6 in |

| | |
|-------------------|--------|
| Product Height US | 4.1 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------|-----|------------|-----|
| FCC Compliant | Yes | cUL Listed | Yes |
|---------------|-----|------------|-----|

Additional Information

| | | | |
|----------------|-----|---|-----|
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
|----------------|-----|---|-----|

Technical Information

| | | | |
|---------------------------|------|-------------|----|
| Operating Temperature Min | 0 °C | Has Battery | No |
|---------------------------|------|-------------|----|

| | | | |
|---------------------------|-------|-------------------|---|
| Operating Temperature Max | 55 °C | Number of Buttons | 2 |
|---------------------------|-------|-------------------|---|

| | | | |
|-------------------|---|---------------|--------|
| Number of Rockers | 0 | Input Voltage | 24 VDC |
|-------------------|---|---------------|--------|

| | | | |
|----------------|--------|--------------|------|
| Indoor/Outdoor | Indoor | Current Draw | 5 mA |
|----------------|--------|--------------|------|

| | | | |
|-----------------------|--------------------|--------------------|------------------------------|
| Operating Temperature | 0°-55°C, 32°-131°F | Operating Humidity | 5-95% RH (Non-Condensing) |
|-----------------------|--------------------|--------------------|------------------------------|

| | | | |
|----------------------|-------|----------------|----------------|
| Wire Connection Type | RJ-45 | Engraving Type | Icon with Text |
|----------------------|-------|----------------|----------------|
