



Wattstopper
Discontinued - PIR Dimmable Wall Switch Sensor, 120/277V, White
 Part No. PW-100D-W



The PW-100D-W passive infrared (PIR) dimmable white wall switch sensor can turn light OFF and ON based on occupancy. It is characterized by high sensitivity to small and large movements, appealing aesthetics, and a variety of features.

Features & Benefits

High sensitivity and dense coverage for exceptional performance	Vandal resistant lens combines precise coverage with durability
Defaults to Manual-ON operation for maximum energy savings	Color-matched lens and low profile for appealing design
Pushbutton dimming control and optional locked preset level for many lighting types	Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience
Part of a comprehensive line of PIR, Ultrasonic and Dual Technology wall switch sensors	Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI
Vandal resistant lens combines precise coverage with durability	Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds
In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations	Selectable audible and/or visual alerts for impending shutoff
2-wire and 3-wire models available for applications with or without neutral wire	Choice of Manual-ON or Auto-ON operation

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	PW-101D-W
Color	White	UPC Number	754182930791
Country Of Origin	China	Features	IR (Infrared), Motion Sensor

Switch Type	Motion Sensor	Application Sector	Commercial
-------------	---------------	--------------------	------------

Warranty Type	5-Year
---------------	--------

Dimensions

Product Width US	2.0 in	Product Weight US	0.4 lb
------------------	--------	-------------------	--------

Product Volume US	27.84 cu in	Product Depth US	4.5 in
-------------------	-------------	------------------	--------

Product Height US	2.25 in
-------------------	---------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Response Frequency	50/60 Hz	Sensor Type	Occupancy
--------------------	----------	-------------	-----------

Number of Buttons	1	Amperage	4.3 A
-------------------	---	----------	-------

Indicator	LED Light	Wattage	1200 W
-----------	-----------	---------	--------

Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Voltage	120/277 V
---------------	--	---------	-----------

Connection Type	Wired
-----------------	-------
