



radiant Collection
radiant® Single Pole/3-Way Fan Speed Control, White
Part No. RHDH163PW



Upgrade your fan control with the sweet sound of silence. Specially designed to virtually eliminate the fan motor "hum." This device provides quieter fan speed control while featuring the sleek, clean lines of radiant® for a sophisticated touch. This fan control switch handles a max load of 1.6A. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

| | |
|--|---|
| Designed to virtually eliminate the motor's hum for quieter use. | Installs easily in place of a standard light or fan control switch. Rated for a max load of 1.6A. |
| Offers installation flexibility, working in both single-pole and 3-way applications. | Returns the fan to its previous level after a power failure. |
| Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. | More color options available to fit any style. |
| Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. | |

Specifications

General Info

| | | | |
|--------------------|---------------------------|--------------------|------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Features | Fan Control |
| Switch Type | Paddle | Number of Switches | 1 |
| Application Sector | Residential | Standard | CSA Listed, cULus, UL Listed |
| Warranty Type | Limited Lifetime Warranty | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 1.25 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.25 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------|------------|----------------|--------|
| Connection | Back Wired | Contact Rating | 120VAC |
|------------|------------|----------------|--------|

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|--------------------|---------------|-----|
| Number of Poles | 3-Way, Single Pole | Mounting Type | Box |
|-----------------|--------------------|---------------|-----|

| | | | |
|-------------|---------|---------|---------|
| Speed Range | 3-Speed | Voltage | 120.0 V |
|-------------|---------|---------|---------|

| | |
|--------------------------|-------------|
| Environmental Conditions | Indoor Only |
|--------------------------|-------------|